



Penal-Ware® 1827 Series Auto-Release Clothes Hooks Panel



1828



1829

Fixture May Show Some Available Options

Please visit www.acorneng.com for most current specifications.

Auto-Release Clothes Hooks Panel

The Acorn Auto-Release Clothes Hooks Panel is recommended for cell, shower room or day rooms. All Models are fabricated of 14 gage type 304 stainless steel with exposed surfaces polished to a satin finish. Auto release hooks are tested to hold a minimum of 20 lbs. and fail at 40 lbs. or greater.

Rear Mount Models are furnished with 1/4"-20 UNC steel studs, heavy washers and nuts for installing onto walls up to 8" thick.

Front Mount Models are furnished with 1/4"-20 UNC tamper-resistant screws for installer provided wall anchors.



Penal-Ware®: 1827 Auto-Release Clothes Hooks Panel

WALL THICKNESS AND TYPE (Must Specify)

Thickness _____ Type: ___ Concrete ___ Block ___ Steel

Product Options


-SW Wall Sleeve

MODEL NUMBER AND OPTIONS SELECTION

BASE MODEL NUMBER

- 1827 Multiple Clothes Hooks Panel, Rear Mount
- 1828 Multiple Clothes Hooks Panel, Front Mount
- 1829 Single Clothes Hook Panel, Rear Mount
- 1830 Single Clothes Hook Panel, Front Mount

Please visit www.acorneng.com for most current specifications.



NOTES:

1. Auto-Release Clothes Hooks.
2. Tamper Resistant Screws.
3. Wall Mounting Hardware.
4. Wall Mounting Anchors (By Others).

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

<p>Important: Installation instructions and current rough-in are furnished with each fixture. Do not rough in without certified dimensions. Dimensions are subject to manufacturer's tolerance of plus or minus 1/4" and change without notice. Acorn assumes no responsibility for use of void or superseded data. © Copyright 2006 Acorn Engineering Company</p>	
<p>Selection Summary</p> <p>Model No. & Option _____</p> <p>Quantity _____</p>	<p>Approved for Manufacturing</p> <p>Company _____ Title _____</p> <p>Signature _____ Date _____</p>